

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211981

Luminaire Tested: **LE_4B30D010 EC4B30509030 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509030 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2961.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211981
CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211981

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211981

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.7	6.5
10°-20°	488.9	16.5
20°-30°	633.6	21.4
30°-40°	620.8	21.0
40°-50°	526.2	17.8
50°-60°	344.9	11.6
60°-70°	138.6	4.7
70°-80°	15.8	0.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1314.2	44.4
0°-40°	1935.0	65.3
0°-60°	2806.0	94.8
0°-90°	2961.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2961.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2114	
5°	2058	192
15°	1744	489
25°	1383	634
35°	987	621
45°	685	526
55°	384	345
65°	134	139
75°	7	16
85°	0	0
90°	0	



TEST NUMBER: P211981

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2114.2
2.5°	2097.9
5°	2058.5
7.5°	1992.9
10°	1911.0
12.5°	1822.5
15°	1743.8
17.5°	1658.6
20°	1573.3
22.5°	1481.6
25°	1383.3
27.5°	1281.7
30°	1176.7
32.5°	1078.5
35°	986.6
37.5°	911.3
40°	829.3
42.5°	757.1
45°	685.1
47.5°	609.7
50°	534.3
52.5°	458.9
55°	383.5
57.5°	314.7
60°	249.2
62.5°	190.1
65°	134.4
67.5°	88.5
70°	52.4
72.5°	23.0
75°	6.6
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)