

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210858

Luminaire Tested: **LE_4B10D010 EC4B10209030 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209030 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 928.9 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210858

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210858

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		93
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85
3	96	87	80	75	93	85	79	74	83	77	73		80	76	72		78
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71
5	83	72	64	59	81	71	64	58	69	63	58		67	62	57		65
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	61	49	42	37	59	48	41	37	47	41	37		46	41	37		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210858

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	5.7
10°-20°	147.8	15.9
20°-30°	208.9	22.5
30°-40°	202.4	21.8
40°-50°	136.5	14.7
50°-60°	84.7	9.1
60°-70°	56.6	6.1
70°-80°	31.0	3.3
80°-90°	8.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	409.6	44.1
0°-40°	611.9	65.9
0°-60°	833.2	89.7
0°-90°	928.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	928.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	563	
5°	558	53
15°	524	148
25°	458	209
35°	326	202
45°	175	137
55°	93	85
65°	57	57
75°	29	31
85°	7	8
90°	0	



TEST NUMBER: P210858

CATALOG NUMBER: LE_4B10D010 EC4B10209030 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	562.9
2.5°	562.9
5°	558.2
7.5°	552.2
10°	544.9
12.5°	537.7
15°	524.4
17.5°	513.5
20°	495.4
22.5°	477.3
25°	458.1
27.5°	431.5
30°	402.6
32.5°	365.3
35°	325.5
37.5°	285.7
40°	245.9
42.5°	206.1
45°	174.8
47.5°	145.8
50°	124.1
52.5°	106.1
55°	92.8
57.5°	82.0
60°	73.5
62.5°	65.1
65°	56.6
67.5°	49.4
70°	42.2
72.5°	36.2
75°	28.9
77.5°	22.9
80°	16.8
82.5°	12.1
85°	7.2
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)