

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211989

Luminaire Tested: **LE_4B30D010 EC4B30509030 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509030 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2524.8 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211989

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211989

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211989

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.7	5.7
10°-20°	401.7	15.9
20°-30°	567.7	22.5
30°-40°	549.9	21.8
40°-50°	371.1	14.7
50°-60°	230.3	9.1
60°-70°	153.9	6.1
70°-80°	84.2	3.3
80°-90°	22.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.1	44.1
0°-40°	1663.0	65.9
0°-60°	2264.4	89.7
0°-90°	2524.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2524.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1530	
5°	1517	144
15°	1425	402
25°	1245	568
35°	885	550
45°	475	371
55°	252	230
65°	154	154
75°	79	84
85°	20	22
90°	0	



TEST NUMBER: P211989

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1530.0
2.5°	1530.0
5°	1516.9
7.5°	1500.5
10°	1480.9
12.5°	1461.1
15°	1425.2
17.5°	1395.7
20°	1346.5
22.5°	1297.3
25°	1244.9
27.5°	1172.9
30°	1094.2
32.5°	992.7
35°	884.6
37.5°	776.5
40°	668.4
42.5°	560.3
45°	475.0
47.5°	396.4
50°	337.4
52.5°	288.3
55°	252.3
57.5°	222.8
60°	199.9
62.5°	176.9
65°	153.9
67.5°	134.3
70°	114.7
72.5°	98.3
75°	78.6
77.5°	62.3
80°	45.8
82.5°	32.7
85°	19.6
87.5°	6.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)