

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211992

Luminaire Tested: **LE\_4B30D010 EC4B30509730 4LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211992  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509730 4LBCS1MMS  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3120.6 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211992

CATALOG NUMBER: LE\_4B30D010 EC4B30509730 4LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P211992

CATALOG NUMBER: LE\_4B30D010 EC4B30509730 4LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211992

CATALOG NUMBER: LE\_4B30D010 EC4B30509730 4LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.1	4.3
10°-20°	379.0	12.1
20°-30°	553.5	17.7
30°-40°	633.1	20.3
40°-50°	608.4	19.5
50°-60°	469.8	15.1
60°-70°	262.2	8.4
70°-80°	76.3	2.4
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1067.5	34.2
0°-40°	1700.6	54.5
0°-60°	2778.8	89.0
0°-90°	3120.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3120.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1433	
5°	1421	135
15°	1344	379
25°	1203	553
35°	1013	633
45°	793	608
55°	527	470
65°	262	262
75°	67	76
85°	2	3
90°	0	



TEST NUMBER: P211992

CATALOG NUMBER: LE\_4B30D010 EC4B30509730 4LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1433.1
2.5°	1433.1
5°	1421.0
7.5°	1415.0
10°	1394.8
12.5°	1370.5
15°	1344.3
17.5°	1318.0
20°	1279.7
22.5°	1249.4
25°	1203.0
27.5°	1156.5
30°	1110.1
32.5°	1063.7
35°	1013.3
37.5°	962.8
40°	904.2
42.5°	851.8
45°	793.2
47.5°	726.6
50°	664.1
52.5°	595.4
55°	526.8
57.5°	456.1
60°	389.5
62.5°	322.9
65°	262.4
67.5°	205.9
70°	153.4
72.5°	107.0
75°	66.6
77.5°	34.3
80°	12.1
82.5°	4.1
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)