

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210947

Luminaire Tested: **LE_4B10D010 EC4B10208040 4LBCSM1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208040 4LBSCM1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1260.7 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210947

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBCSM1B

Luminous Intensity Polar Plot





TEST NUMBER: P210947

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBCSM1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	104	101	98	100	98	95		96	94	92		93
2	102	95	89	84	99	93	87	83	89	85	81		86	82	79		83
3	93	84	77	71	91	83	76	70	80	74	69		77	72	68		74
4	86	75	67	61	84	74	66	61	71	65	60		69	63	59		67
5	79	67	59	53	77	66	59	53	64	57	52		62	56	52		61
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	55	47	41	67	55	47	41	53	46	41		52	45	41		50
8	64	51	43	37	62	50	42	37	49	42	37		48	41	37		46
9	60	47	39	33	58	46	39	33	45	38	33		44	38	33		43
10	56	43	35	30	55	43	35	30	42	35	30		41	34	30		40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210947

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBCSM1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	4.0
10°-20°	143.5	11.4
20°-30°	215.7	17.1
30°-40°	255.9	20.3
40°-50°	253.2	20.1
50°-60°	198.9	15.8
60°-70°	111.5	8.8
70°-80°	31.3	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	409.5	32.5
0°-40°	665.3	52.8
0°-60°	1117.4	88.6
0°-90°	1260.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1260.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	532	
5°	531	50
15°	509	143
25°	468	216
35°	410	256
45°	330	253
55°	224	199
65°	111	112
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P210947

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBCSM1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	532.3
2.5°	530.6
5°	531.4
7.5°	526.9
10°	521.5
12.5°	515.2
15°	508.9
17.5°	500.8
20°	489.9
22.5°	479.1
25°	468.2
27.5°	456.5
30°	441.0
32.5°	425.7
35°	410.3
37.5°	392.3
40°	371.4
42.5°	351.6
45°	329.9
47.5°	305.5
50°	280.1
52.5°	251.3
55°	224.1
57.5°	193.4
60°	164.5
62.5°	138.3
65°	111.1
67.5°	87.7
70°	65.1
72.5°	44.3
75°	27.1
77.5°	13.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)