

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212013

Luminaire Tested: **LE_4B30D010 EC4B30509730 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509730 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3524.3 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212013

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P212013

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212013

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.5	5.9
10°-20°	547.1	15.5
20°-30°	734.8	20.8
30°-40°	752.1	21.3
40°-50°	651.0	18.5
50°-60°	433.0	12.3
60°-70°	177.8	5.0
70°-80°	21.2	0.6
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1488.3	42.2
0°-40°	2240.4	63.6
0°-60°	3324.4	94.3
0°-90°	3524.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3524.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2234	
5°	2199	206
15°	1954	547
25°	1603	735
35°	1201	752
45°	848	651
55°	480	433
65°	176	178
75°	9	21
85°	0	1
90°	0	



TEST NUMBER: P212013

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2233.7
2.5°	2229.1
5°	2199.1
7.5°	2152.8
10°	2090.6
12.5°	2021.2
15°	1954.3
17.5°	1868.8
20°	1785.6
22.5°	1697.8
25°	1603.1
27.5°	1501.5
30°	1399.8
32.5°	1298.2
35°	1201.2
37.5°	1108.7
40°	1021.0
42.5°	933.2
45°	847.7
47.5°	757.7
50°	665.3
52.5°	572.9
55°	480.5
57.5°	399.6
60°	316.4
62.5°	240.2
65°	175.5
67.5°	115.5
70°	66.9
72.5°	32.4
75°	9.3
77.5°	4.6
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)