

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210966

Luminaire Tested: **LE_4B10D010 EC4B10208040 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208040 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1321.6 lumens
Efficiency: N/A
Efficacy: 133.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210966

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P210966

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80	
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71	
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57	
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51	
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42	
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210966

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.6	6.5
10°-20°	218.2	16.5
20°-30°	282.8	21.4
30°-40°	277.1	21.0
40°-50°	234.8	17.8
50°-60°	154.0	11.7
60°-70°	61.9	4.7
70°-80°	7.1	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.5	44.4
0°-40°	863.6	65.3
0°-60°	1252.4	94.8
0°-90°	1321.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	944	
5°	919	86
15°	778	218
25°	617	283
35°	440	277
45°	306	235
55°	171	154
65°	60	62
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P210966

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.7
2.5°	936.2
5°	918.7
7.5°	889.5
10°	852.9
12.5°	813.4
15°	778.2
17.5°	740.3
20°	702.3
22.5°	661.2
25°	617.4
27.5°	572.0
30°	525.2
32.5°	481.3
35°	440.3
37.5°	406.7
40°	370.2
42.5°	337.9
45°	305.8
47.5°	272.1
50°	238.5
52.5°	204.9
55°	171.2
57.5°	140.5
60°	111.1
62.5°	84.8
65°	60.0
67.5°	39.6
70°	23.4
72.5°	10.2
75°	2.9
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)