

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212022

Luminaire Tested: **LE_4B30D010 EC4B30508035 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508035 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3619.7 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212022

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212022

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212022

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	3.9
10°-20°	398.8	11.0
20°-30°	599.9	16.6
30°-40°	710.9	19.6
40°-50°	707.5	19.5
50°-60°	570.3	15.8
60°-70°	345.0	9.5
70°-80°	128.1	3.5
80°-90°	19.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1138.7	31.5
0°-40°	1849.7	51.1
0°-60°	3127.5	86.4
0°-90°	3619.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3619.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1478	
5°	1472	140
15°	1412	399
25°	1303	600
35°	1138	711
45°	921	707
55°	636	570
65°	347	345
75°	116	128
85°	15	19
90°	0	



TEST NUMBER: P212022

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1478.4
2.5°	1478.4
5°	1471.8
7.5°	1467.4
10°	1454.3
12.5°	1432.4
15°	1412.5
17.5°	1390.6
20°	1364.3
22.5°	1338.1
25°	1302.9
27.5°	1265.7
30°	1223.9
32.5°	1184.5
35°	1138.4
37.5°	1090.2
40°	1033.1
42.5°	978.2
45°	921.3
47.5°	857.6
50°	787.4
52.5°	715.0
55°	636.1
57.5°	566.0
60°	487.0
62.5°	416.8
65°	346.6
67.5°	280.7
70°	219.4
72.5°	164.5
75°	116.2
77.5°	74.6
80°	43.8
82.5°	26.3
85°	15.3
87.5°	6.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)