

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210999

Luminaire Tested: **LE_4B10D010 EC4B10209040 4LBW1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209040 4LBW1B
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 528.2 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210999

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1B

Luminous Intensity Polar Plot





TEST NUMBER: P210999

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																												
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86																												
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																												
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72																												
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67																												
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62																												
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57																												
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																												
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49																												
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210999

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	7.9
10°-20°	118.0	22.3
20°-30°	163.0	30.9
30°-40°	139.6	26.4
40°-50°	59.3	11.2
50°-60°	6.6	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.6	61.1
0°-40°	462.2	87.5
0°-60°	528.2	100.0
0°-90°	528.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	441	
5°	438	42
15°	419	118
25°	358	163
35°	226	140
45°	75	59
55°	4	7
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210999

CATALOG NUMBER: LE_4B10D010 EC4B10209040 4LBW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	440.9
2.5°	439.8
5°	438.5
7.5°	436.0
10°	431.2
12.5°	428.6
15°	418.9
17.5°	410.3
20°	396.8
22.5°	380.9
25°	357.6
27.5°	331.9
30°	302.5
32.5°	267.0
35°	226.5
37.5°	184.9
40°	143.3
42.5°	106.6
45°	74.7
47.5°	46.5
50°	26.9
52.5°	13.5
55°	3.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)