

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211006

Luminaire Tested: **LE\_4B10D010 EC4B10208050 4LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B10D010 EC4B10208050 4LBCS1MMS  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1137.6 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211006

CATALOG NUMBER: LE\_4B10D010 EC4B10208050 4LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P211006

CATALOG NUMBER: LE\_4B10D010 EC4B10208050 4LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211006

CATALOG NUMBER: LE\_4B10D010 EC4B10208050 4LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.2	4.3
10°-20°	138.1	12.1
20°-30°	201.8	17.7
30°-40°	230.8	20.3
40°-50°	221.8	19.5
50°-60°	171.3	15.1
60°-70°	95.6	8.4
70°-80°	27.8	2.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.1	34.2
0°-40°	619.9	54.5
0°-60°	1013.0	89.0
0°-90°	1137.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1137.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	522	
5°	518	49
15°	490	138
25°	438	202
35°	369	231
45°	289	222
55°	192	171
65°	96	96
75°	24	28
85°	1	1
90°	0	



TEST NUMBER: P211006

CATALOG NUMBER: LE\_4B10D010 EC4B10208050 4LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	522.5
2.5°	522.5
5°	517.9
7.5°	515.7
10°	508.4
12.5°	499.6
15°	490.0
17.5°	480.5
20°	466.4
22.5°	455.4
25°	438.5
27.5°	421.7
30°	404.7
32.5°	387.8
35°	369.3
37.5°	351.0
40°	329.7
42.5°	310.5
45°	289.2
47.5°	264.8
50°	242.1
52.5°	217.0
55°	192.1
57.5°	166.3
60°	142.0
62.5°	117.7
65°	95.7
67.5°	75.1
70°	55.9
72.5°	39.0
75°	24.2
77.5°	12.5
80°	4.4
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)