

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212031

Luminaire Tested: **LE_4B30D010 EC4B30508035 4LBN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508035 4LBN1H
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2168.0 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212031

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBN1H

Luminous Intensity Polar Plot





TEST NUMBER: P212031

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212031

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.6	11.3
10°-20°	595.7	27.5
20°-30°	691.6	31.9
30°-40°	458.0	21.1
40°-50°	128.5	5.9
50°-60°	32.3	1.5
60°-70°	12.1	0.6
70°-80°	4.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1532.9	70.7
0°-40°	1991.0	91.8
0°-60°	2151.7	99.3
0°-90°	2168.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2168.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2722	
5°	2651	246
15°	2133	596
25°	1516	692
35°	734	458
45°	149	128
55°	35	32
65°	12	12
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P212031

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2721.9
2.5°	2710.2
5°	2651.3
7.5°	2549.1
10°	2423.5
12.5°	2282.1
15°	2132.8
17.5°	1987.4
20°	1826.4
22.5°	1677.1
25°	1516.1
27.5°	1363.0
30°	1166.6
32.5°	958.4
35°	734.5
37.5°	526.3
40°	357.4
42.5°	231.8
45°	149.3
47.5°	90.4
50°	58.9
52.5°	43.2
55°	35.4
57.5°	27.5
60°	19.6
62.5°	15.7
65°	11.8
67.5°	7.9
70°	7.9
72.5°	3.9
75°	3.9
77.5°	3.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)