

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212034

Luminaire Tested: **LE\_4B30D010 EC4B30508035 4LBN1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212034  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30508035 4LBN1WH  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2278.1 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212034

CATALOG NUMBER: LE\_4B30D010 EC4B30508035 4LBN1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P212034

CATALOG NUMBER: LE\_4B30D010 EC4B30508035 4LBN1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84		
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79		
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61		
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212034

CATALOG NUMBER: LE\_4B30D010 EC4B30508035 4LBN1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	395.9	17.4
10°-20°	742.7	32.6
20°-30°	666.4	29.3
30°-40°	382.4	16.8
40°-50°	76.3	3.3
50°-60°	9.7	0.4
60°-70°	4.4	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1804.9	79.2
0°-40°	2187.3	96.0
0°-60°	2273.3	99.8
0°-90°	2278.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2278.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4842	
5°	4452	396
15°	2667	743
25°	1439	666
35°	606	382
45°	83	76
55°	12	10
65°	4	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P212034

CATALOG NUMBER: LE\_4B30D010 EC4B30508035 4LBN1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4841.6
2.5°	4743.2
5°	4452.2
7.5°	4027.4
10°	3563.3
12.5°	3107.1
15°	2666.6
17.5°	2281.1
20°	1950.8
22.5°	1675.5
25°	1439.4
27.5°	1250.7
30°	1042.3
32.5°	829.9
35°	605.6
37.5°	413.0
40°	255.7
42.5°	153.4
45°	82.6
47.5°	35.4
50°	15.8
52.5°	11.8
55°	11.8
57.5°	7.9
60°	7.9
62.5°	3.9
65°	3.9
67.5°	3.9
70°	3.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)