

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211047

Luminaire Tested: **LE_4B10D010 EC4B10209050 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209050 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 774.2 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211047

CATALOG NUMBER: LE_4B10D010 EC4B10209050 4LBN1MW

Luminous Intensity Polar Plot






TEST NUMBER: P211047

CATALOG NUMBER: LE_4B10D010 EC4B10209050 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	105	103		109	106	104	101		102	100	98		98	97	95		95	94	92
2	105	99	94	90		103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	80		96	89	83	79		86	82	78		84	80	76		81	78	75
4	92	83	76	71		90	82	76	71		80	74	70		78	73	69		76	72	68
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	63
6	82	71	64	59		80	70	64	59		69	63	58		67	62	58		66	61	58
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		62	57	53
8	73	62	55	50		71	61	55	50		60	54	50		59	53	49		58	53	49
9	69	58	51	46		68	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	48	43		64	54	47	43		53	47	43		52	47	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211047

CATALOG NUMBER: LE_4B10D010 EC4B10209050 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.8	7.8
10°-20°	159.0	20.5
20°-30°	209.2	27.0
30°-40°	162.9	21.0
40°-50°	79.1	10.2
50°-60°	50.0	6.5
60°-70°	32.2	4.2
70°-80°	16.9	2.2
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.0	55.4
0°-40°	591.9	76.4
0°-60°	720.9	93.1
0°-90°	774.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	648	61
15°	567	159
25°	461	209
35°	261	163
45°	98	79
55°	55	50
65°	32	32
75°	16	17
85°	4	4
90°	0	



TEST NUMBER: P211047

CATALOG NUMBER: LE_4B10D010 EC4B10209050 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.5
2.5°	656.8
5°	648.2
7.5°	633.4
10°	613.8
12.5°	591.6
15°	567.0
17.5°	541.1
20°	514.1
22.5°	488.2
25°	461.2
27.5°	426.8
30°	380.0
32.5°	324.7
35°	260.8
37.5°	201.7
40°	156.3
42.5°	121.8
45°	98.4
47.5°	79.9
50°	70.1
52.5°	62.8
55°	55.3
57.5°	49.2
60°	43.0
62.5°	36.9
65°	32.0
67.5°	28.3
70°	23.3
72.5°	19.7
75°	16.0
77.5°	12.3
80°	8.6
82.5°	6.1
85°	3.7
87.5°	1.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)