

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212070

Luminaire Tested: **LE\_4B30D010 EC4B30509035 4LBS1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212070  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509035 4LBS1WH  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2895.7 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212070

CATALOG NUMBER: LE\_4B30D010 EC4B30509035 4LBS1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P212070

CATALOG NUMBER: LE\_4B30D010 EC4B30509035 4LBS1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212070

CATALOG NUMBER: LE\_4B30D010 EC4B30509035 4LBS1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.3	5.5
10°-20°	412.3	14.2
20°-30°	539.3	18.6
30°-40°	571.0	19.7
40°-50°	532.6	18.4
50°-60°	403.4	13.9
60°-70°	218.5	7.5
70°-80°	58.6	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1110.8	38.4
0°-40°	1681.8	58.1
0°-60°	2617.7	90.4
0°-90°	2895.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2895.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1727	
5°	1702	159
15°	1473	412
25°	1172	539
35°	913	571
45°	694	533
55°	453	403
65°	219	218
75°	51	59
85°	0	1
90°	0	



TEST NUMBER: P212070

CATALOG NUMBER: LE\_4B30D010 EC4B30509035 4LBS1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1727.0
2.5°	1720.6
5°	1701.6
7.5°	1660.4
10°	1606.6
12.5°	1543.1
15°	1473.4
17.5°	1394.3
20°	1324.6
22.5°	1245.4
25°	1172.4
27.5°	1099.6
30°	1029.8
32.5°	969.6
35°	912.6
37.5°	855.6
40°	801.7
42.5°	747.9
45°	693.9
47.5°	633.7
50°	573.5
52.5°	513.3
55°	453.1
57.5°	389.8
60°	329.6
62.5°	272.5
65°	218.7
67.5°	168.0
70°	123.5
72.5°	85.6
75°	50.7
77.5°	22.2
80°	6.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)