

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212080

Luminaire Tested: **LE_4B30D010 EC4B30508040 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508040 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3658.7 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212080

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212080

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212080

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.6	3.9
10°-20°	403.1	11.0
20°-30°	606.3	16.6
30°-40°	718.6	19.6
40°-50°	715.1	19.5
50°-60°	576.5	15.8
60°-70°	348.8	9.5
70°-80°	129.5	3.5
80°-90°	19.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1151.0	31.5
0°-40°	1869.6	51.1
0°-60°	3161.2	86.4
0°-90°	3658.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3658.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1494	
5°	1488	142
15°	1428	403
25°	1317	606
35°	1151	719
45°	931	715
55°	643	576
65°	350	349
75°	118	129
85°	16	19
90°	0	



TEST NUMBER: P212080

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1494.3
2.5°	1494.3
5°	1487.7
7.5°	1483.3
10°	1470.0
12.5°	1447.8
15°	1427.8
17.5°	1405.7
20°	1379.1
22.5°	1352.4
25°	1316.9
27.5°	1279.2
30°	1237.1
32.5°	1197.2
35°	1150.7
37.5°	1101.9
40°	1044.2
42.5°	988.9
45°	931.2
47.5°	866.9
50°	796.0
52.5°	722.8
55°	643.0
57.5°	572.0
60°	492.2
62.5°	421.3
65°	350.3
67.5°	283.9
70°	221.7
72.5°	166.3
75°	117.5
77.5°	75.4
80°	44.3
82.5°	26.6
85°	15.5
87.5°	6.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)