

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211097

Luminaire Tested: **LE\_4B15D010 EC4B10208027 4LBM1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211097  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B15D010 EC4B10208027 4LBM1H  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1247.9 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211097

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBM1H

### Luminous Intensity Polar Plot





TEST NUMBER: P211097

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBM1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 95  | 93  |    |    |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  | 88  | 84  | 82  | 86  | 83  | 80  | 79  |    |    |
| 4   | 96  | 88  | 82  | 77  | 94  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 78  | 75  | 80  | 77  | 74  | 73  |    |    |
| 5   | 90  | 82  | 75  | 71  | 89  | 81  | 75  | 70  | 79  | 74  | 70  | 77  | 73  | 69  | 75  | 72  | 69  | 67  |    |    |
| 6   | 86  | 76  | 70  | 65  | 84  | 75  | 69  | 65  | 74  | 68  | 64  | 72  | 68  | 64  | 71  | 67  | 64  | 62  |    |    |
| 7   | 81  | 71  | 65  | 60  | 80  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 59  | 67  | 62  | 59  | 58  |    |    |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  | 64  | 59  | 55  | 63  | 58  | 55  | 54  |    |    |
| 9   | 73  | 63  | 56  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 59  | 55  | 52  | 50  |    |    |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 52  | 49  | 57  | 52  | 48  | 56  | 52  | 48  | 47  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211097

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBM1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 113.9  | 9.1       |
| 10°-20°   | 298.7  | 23.9      |
| 20°-30°   | 383.9  | 30.8      |
| 30°-40°   | 288.8  | 23.1      |
| 40°-50°   | 116.0  | 9.3       |
| 50°-60°   | 33.0   | 2.6       |
| 60°-70°   | 10.4   | 0.8       |
| 70°-80°   | 3.0    | 0.2       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 796.5  | 63.8      |
| 0°-40°    | 1085.3 | 87.0      |
| 0°-60°    | 1234.3 | 98.9      |
| 0°-90°    | 1247.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1247.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1238 |      |
| 5°  | 1215 | 114  |
| 15° | 1066 | 299  |
| 25° | 848  | 384  |
| 35° | 463  | 289  |
| 45° | 143  | 116  |
| 55° | 34   | 33   |
| 65° | 9    | 10   |
| 75° | 2    | 3    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P211097

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBM1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1237.5 |
| 2.5°  | 1229.9 |
| 5°    | 1214.9 |
| 7.5°  | 1186.6 |
| 10°   | 1150.8 |
| 12.5° | 1107.5 |
| 15°   | 1066.0 |
| 17.5° | 1018.9 |
| 20°   | 968.1  |
| 22.5° | 913.5  |
| 25°   | 847.6  |
| 27.5° | 768.5  |
| 30°   | 676.2  |
| 32.5° | 572.6  |
| 35°   | 463.3  |
| 37.5° | 361.6  |
| 40°   | 271.2  |
| 42.5° | 199.6  |
| 45°   | 143.1  |
| 47.5° | 97.9   |
| 50°   | 67.9   |
| 52.5° | 47.1   |
| 55°   | 33.9   |
| 57.5° | 24.5   |
| 60°   | 18.8   |
| 62.5° | 13.2   |
| 65°   | 9.4    |
| 67.5° | 7.5    |
| 70°   | 5.7    |
| 72.5° | 3.7    |
| 75°   | 1.9    |
| 77.5° | 1.9    |
| 80°   | 1.9    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)