

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212105

Luminaire Tested: **LE_4B30D010 EC4B30508040 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508040 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3062.5 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212105

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212105

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212105

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.2	5.7
10°-20°	487.2	15.9
20°-30°	688.6	22.5
30°-40°	667.0	21.8
40°-50°	450.1	14.7
50°-60°	279.3	9.1
60°-70°	186.7	6.1
70°-80°	102.2	3.3
80°-90°	27.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.1	44.1
0°-40°	2017.1	65.9
0°-60°	2746.5	89.7
0°-90°	3062.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3062.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1856	
5°	1840	174
15°	1728	487
25°	1510	689
35°	1073	667
45°	576	450
55°	306	279
65°	187	187
75°	95	102
85°	24	27
90°	0	



TEST NUMBER: P212105

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1855.8
2.5°	1855.8
5°	1839.9
7.5°	1819.9
10°	1796.1
12.5°	1772.2
15°	1728.5
17.5°	1692.8
20°	1633.2
22.5°	1573.5
25°	1510.0
27.5°	1422.6
30°	1327.3
32.5°	1204.1
35°	1072.9
37.5°	941.8
40°	810.6
42.5°	679.5
45°	576.2
47.5°	480.8
50°	409.2
52.5°	349.7
55°	306.0
57.5°	270.2
60°	242.4
62.5°	214.6
65°	186.8
67.5°	163.0
70°	139.1
72.5°	119.2
75°	95.4
77.5°	75.5
80°	55.7
82.5°	39.8
85°	23.9
87.5°	8.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)