

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212111

Luminaire Tested: **LE\_4B30D010 EC4B30509040 4LBM1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212111  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509040 4LBM1GPH  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1585.9 lumens  
Efficiency: N/A  
Efficacy: 56.6 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212111

CATALOG NUMBER: LE\_4B30D010 EC4B30509040 4LBM1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P212111

CATALOG NUMBER: LE\_4B30D010 EC4B30509040 4LBM1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212111

CATALOG NUMBER: LE\_4B30D010 EC4B30509040 4LBM1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.0	9.5
10°-20°	391.2	24.7
20°-30°	501.8	31.6
30°-40°	362.7	22.9
40°-50°	130.0	8.2
50°-60°	35.1	2.2
60°-70°	11.5	0.7
70°-80°	3.6	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.0	65.8
0°-40°	1405.7	88.6
0°-60°	1570.9	99.1
0°-90°	1585.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1585.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1630	
5°	1600	150
15°	1394	391
25°	1107	502
35°	580	363
45°	157	130
55°	37	35
65°	10	11
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P212111

CATALOG NUMBER: LE\_4B30D010 EC4B30509040 4LBM1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1630.4
2.5°	1623.7
5°	1600.3
7.5°	1563.7
10°	1513.7
12.5°	1457.0
15°	1393.6
17.5°	1330.3
20°	1267.0
22.5°	1193.6
25°	1106.9
27.5°	1006.9
30°	880.2
32.5°	733.5
35°	580.1
37.5°	440.1
40°	320.0
42.5°	226.7
45°	156.7
47.5°	106.7
50°	70.1
52.5°	50.0
55°	36.7
57.5°	26.7
60°	20.0
62.5°	16.7
65°	10.0
67.5°	6.6
70°	6.6
72.5°	3.4
75°	3.4
77.5°	3.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)