

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211107

Luminaire Tested: **LE_4B15D010 EC4B10208027 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208027 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1769.4 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211107

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211107

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211107

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.5	3.8
10°-20°	192.5	10.9
20°-30°	290.0	16.4
30°-40°	345.0	19.5
40°-50°	344.4	19.5
50°-60°	280.1	15.8
60°-70°	172.3	9.7
70°-80°	66.7	3.8
80°-90°	10.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	550.1	31.1
0°-40°	895.1	50.6
0°-60°	1519.6	85.9
0°-90°	1769.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1769.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	713	
5°	711	68
15°	684	193
25°	631	290
35°	552	345
45°	448	344
55°	313	280
65°	173	172
75°	61	67
85°	8	11
90°	0	



TEST NUMBER: P211107

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	712.9
2.5°	714.0
5°	710.8
7.5°	706.6
10°	701.3
12.5°	691.9
15°	683.6
17.5°	670.9
20°	657.4
22.5°	644.7
25°	631.2
27.5°	612.2
30°	593.3
32.5°	575.6
35°	552.5
37.5°	527.3
40°	504.3
42.5°	475.9
45°	447.6
47.5°	417.3
50°	384.8
52.5°	351.2
55°	313.4
57.5°	276.8
60°	241.2
62.5°	206.5
65°	173.0
67.5°	141.5
70°	112.2
72.5°	84.9
75°	60.8
77.5°	39.8
80°	24.1
82.5°	14.7
85°	8.4
87.5°	4.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)