

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212118

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBN1H
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1835.7 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212118

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1H

Luminous Intensity Polar Plot





TEST NUMBER: P212118

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212118

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.0	11.3
10°-20°	504.4	27.5
20°-30°	585.6	31.9
30°-40°	387.8	21.1
40°-50°	108.8	5.9
50°-60°	27.3	1.5
60°-70°	10.2	0.6
70°-80°	3.6	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.0	70.7
0°-40°	1685.8	91.8
0°-60°	1821.9	99.2
0°-90°	1835.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1835.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2305	
5°	2245	208
15°	1806	504
25°	1284	586
35°	622	388
45°	126	109
55°	30	27
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P212118

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2304.8
2.5°	2294.8
5°	2244.9
7.5°	2158.5
10°	2052.0
12.5°	1932.3
15°	1805.9
17.5°	1682.9
20°	1546.5
22.5°	1420.2
25°	1283.8
27.5°	1154.1
30°	987.7
32.5°	811.5
35°	621.9
37.5°	445.7
40°	302.6
42.5°	196.3
45°	126.4
47.5°	76.4
50°	49.9
52.5°	36.5
55°	29.9
57.5°	23.3
60°	16.6
62.5°	13.3
65°	10.0
67.5°	6.6
70°	6.6
72.5°	3.4
75°	3.4
77.5°	3.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)