

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211116

Luminaire Tested: **LE\_4B15D010 EC4B10208027 4LBW1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211116  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B15D010 EC4B10208027 4LBW1GPH  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1086.1 lumens  
Efficiency: N/A  
Efficacy: 75.9 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211116

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBW1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P211116

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBW1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211116

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBW1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.7	6.8
10°-20°	209.0	19.2
20°-30°	299.7	27.6
30°-40°	282.2	26.0
40°-50°	155.8	14.3
50°-60°	50.0	4.6
60°-70°	12.5	1.1
70°-80°	3.0	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.4	53.6
0°-40°	864.5	79.6
0°-60°	1070.3	98.6
0°-90°	1086.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	782	
5°	778	74
15°	740	209
25°	657	300
35°	458	282
45°	198	156
55°	51	50
65°	11	12
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211116

CATALOG NUMBER: LE\_4B15D010 EC4B10208027 4LBW1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	781.7
2.5°	776.0
5°	777.9
7.5°	772.3
10°	762.8
12.5°	753.4
15°	740.3
17.5°	728.9
20°	710.2
22.5°	683.7
25°	657.4
27.5°	621.6
30°	574.5
32.5°	521.8
35°	457.7
37.5°	389.9
40°	320.2
42.5°	256.1
45°	197.8
47.5°	148.8
50°	107.4
52.5°	75.4
55°	50.8
57.5°	33.9
60°	24.5
62.5°	16.9
65°	11.3
67.5°	7.5
70°	5.7
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)