

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211119

Luminaire Tested: **LE_4B15D010 EC4B10208027 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208027 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1449.2 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211119

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211119

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		93
2	103	96	91	86	101	94	89	85	91	87	83		88	84	81		85
3	96	87	80	75	93	85	79	74	83	77	73		80	76	72		78
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71
5	83	72	64	59	81	71	64	58	69	63	58		67	62	57		65
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56
8	68	56	49	44	67	56	49	44	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	61	49	42	37	59	48	41	37	47	41	37		46	41	37		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211119

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	5.7
10°-20°	230.6	15.9
20°-30°	325.9	22.5
30°-40°	315.7	21.8
40°-50°	213.0	14.7
50°-60°	132.2	9.1
60°-70°	88.3	6.1
70°-80°	48.3	3.3
80°-90°	12.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.0	44.1
0°-40°	954.6	65.9
0°-60°	1299.8	89.7
0°-90°	1449.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1449.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	878	
5°	871	82
15°	818	231
25°	715	326
35°	508	316
45°	273	213
55°	145	132
65°	88	88
75°	45	48
85°	11	13
90°	0	



TEST NUMBER: P211119

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	878.2
2.5°	878.2
5°	870.7
7.5°	861.3
10°	850.0
12.5°	838.8
15°	818.1
17.5°	801.2
20°	772.9
22.5°	744.7
25°	714.7
27.5°	673.3
30°	628.1
32.5°	569.8
35°	507.7
37.5°	445.7
40°	383.6
42.5°	321.6
45°	272.7
47.5°	227.6
50°	193.7
52.5°	165.5
55°	144.8
57.5°	127.8
60°	114.7
62.5°	101.5
65°	88.4
67.5°	77.1
70°	65.8
72.5°	56.4
75°	45.1
77.5°	35.7
80°	26.3
82.5°	18.8
85°	11.3
87.5°	3.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)