

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212127

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3008.4 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212127

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212127

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212127

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	3.8
10°-20°	327.4	10.9
20°-30°	493.0	16.4
30°-40°	586.7	19.5
40°-50°	585.6	19.5
50°-60°	476.2	15.8
60°-70°	292.9	9.7
70°-80°	113.5	3.8
80°-90°	18.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.3	31.1
0°-40°	1521.9	50.6
0°-60°	2583.8	85.9
0°-90°	3008.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3008.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1212	
5°	1208	115
15°	1162	327
25°	1073	493
35°	939	587
45°	761	586
55°	533	476
65°	294	293
75°	103	113
85°	14	18
90°	0	



TEST NUMBER: P212127

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1212.1
2.5°	1213.9
5°	1208.5
7.5°	1201.4
10°	1192.5
12.5°	1176.5
15°	1162.2
17.5°	1140.9
20°	1117.7
22.5°	1096.2
25°	1073.1
27.5°	1041.0
30°	1008.9
32.5°	978.6
35°	939.4
37.5°	896.6
40°	857.4
42.5°	809.2
45°	761.1
47.5°	709.5
50°	654.1
52.5°	597.2
55°	533.0
57.5°	470.6
60°	409.9
62.5°	351.1
65°	294.1
67.5°	240.6
70°	190.7
72.5°	144.4
75°	103.4
77.5°	67.7
80°	40.9
82.5°	24.9
85°	14.3
87.5°	7.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)