

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212130

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBW1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBW1B
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1435.9 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212130
CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBW1B

Luminous Intensity Polar Plot





TEST NUMBER: P212130

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79		
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67		
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62		
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212130

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.2	7.9
10°-20°	320.7	22.3
20°-30°	443.2	30.9
30°-40°	379.5	26.4
40°-50°	161.3	11.2
50°-60°	18.0	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.1	61.1
0°-40°	1256.5	87.5
0°-60°	1435.9	100.0
0°-90°	1435.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1435.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1199	
5°	1192	113
15°	1139	321
25°	972	443
35°	616	379
45°	203	161
55°	10	18
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212130

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1198.6
2.5°	1195.3
5°	1192.0
7.5°	1185.3
10°	1171.9
12.5°	1165.3
15°	1138.7
17.5°	1115.3
20°	1078.8
22.5°	1035.4
25°	972.2
27.5°	902.2
30°	822.4
32.5°	725.8
35°	616.0
37.5°	502.7
40°	389.5
42.5°	289.7
45°	203.1
47.5°	126.6
50°	73.2
52.5°	36.7
55°	10.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)