

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211140

Luminaire Tested: **LE_4B15D010 EC4B10209027 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209027 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1459.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211140

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1LI

Luminous Intensity Polar Plot






TEST NUMBER: P211140

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88	102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77	95	87	81	77		84	79	75		82	78	74		79	76	73
4	90	81	73	68	88	79	73	68		77	71	67		75	70	66		73	69	65
5	84	73	66	61	82	72	65	60		70	64	60		69	63	59		67	62	59
6	79	67	60	54	77	66	59	54		65	58	54		63	58	53		62	57	53
7	74	62	54	49	72	61	54	49		60	53	49		58	53	48		57	52	48
8	69	57	50	45	68	57	50	45		55	49	45		54	49	44		53	48	44
9	65	53	46	41	64	53	46	41		52	45	41		51	45	41		50	44	41
10	61	50	43	38	60	49	42	38		48	42	38		47	42	38		46	41	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211140

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	6.5
10°-20°	241.0	16.5
20°-30°	312.2	21.4
30°-40°	306.0	21.0
40°-50°	259.3	17.8
50°-60°	170.0	11.6
60°-70°	68.3	4.7
70°-80°	7.8	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	647.7	44.4
0°-40°	953.7	65.4
0°-60°	1383.0	94.8
0°-90°	1459.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1459.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1014	94
15°	859	241
25°	682	312
35°	486	306
45°	338	259
55°	189	170
65°	66	68
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P211140

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1042.0
2.5°	1033.9
5°	1014.5
7.5°	982.3
10°	941.9
12.5°	898.3
15°	859.4
17.5°	817.5
20°	775.5
22.5°	730.2
25°	681.7
27.5°	631.7
30°	580.0
32.5°	531.5
35°	486.3
37.5°	449.2
40°	408.8
42.5°	373.2
45°	337.7
47.5°	300.4
50°	263.3
52.5°	226.2
55°	189.0
57.5°	155.1
60°	122.7
62.5°	93.7
65°	66.2
67.5°	43.6
70°	25.9
72.5°	11.3
75°	3.2
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)