

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211141

Luminaire Tested: **LE_4B15D010 EC4B10209027 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209027 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1459.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211141

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211141

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211141

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	3.8
10°-20°	158.8	10.9
20°-30°	239.1	16.4
30°-40°	284.6	19.5
40°-50°	284.1	19.5
50°-60°	231.0	15.8
60°-70°	142.1	9.7
70°-80°	55.0	3.8
80°-90°	8.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	453.7	31.1
0°-40°	738.2	50.6
0°-60°	1253.4	85.9
0°-90°	1459.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1459.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	588	
5°	586	56
15°	564	159
25°	520	239
35°	456	285
45°	369	284
55°	259	231
65°	143	142
75°	50	55
85°	7	9
90°	0	



TEST NUMBER: P211141

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	588.0
2.5°	588.8
5°	586.3
7.5°	582.8
10°	578.5
12.5°	570.7
15°	563.8
17.5°	553.4
20°	542.2
22.5°	531.7
25°	520.5
27.5°	504.9
30°	489.4
32.5°	474.7
35°	455.6
37.5°	434.9
40°	415.9
42.5°	392.5
45°	369.2
47.5°	344.2
50°	317.4
52.5°	289.7
55°	258.6
57.5°	228.3
60°	198.8
62.5°	170.3
65°	142.7
67.5°	116.7
70°	92.6
72.5°	70.1
75°	50.1
77.5°	32.8
80°	19.8
82.5°	12.1
85°	7.0
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)