

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212150

Luminaire Tested: **LE_4B30D010 EC4B30508050 4LBN1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508050 4LBN1WH
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2301.4 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212150

CATALOG NUMBER: LE_4B30D010 EC4B30508050 4LBN1WH

Luminous Intensity Polar Plot





TEST NUMBER: P212150

CATALOG NUMBER: LE_4B30D010 EC4B30508050 4LBN1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89		
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84		
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79		
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75		
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71		
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67		
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64		
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61		
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212150

CATALOG NUMBER: LE_4B30D010 EC4B30508050 4LBN1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.0	17.4
10°-20°	750.3	32.6
20°-30°	673.2	29.3
30°-40°	386.3	16.8
40°-50°	77.0	3.3
50°-60°	9.7	0.4
60°-70°	4.4	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1823.4	79.2
0°-40°	2209.7	96.0
0°-60°	2296.5	99.8
0°-90°	2301.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2301.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4891	
5°	4498	400
15°	2694	750
25°	1454	673
35°	612	386
45°	83	77
55°	12	10
65°	4	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P212150

CATALOG NUMBER: LE_4B30D010 EC4B30508050 4LBN1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4891.1
2.5°	4791.8
5°	4497.8
7.5°	4068.7
10°	3599.8
12.5°	3138.8
15°	2693.9
17.5°	2304.5
20°	1970.7
22.5°	1692.7
25°	1454.2
27.5°	1263.5
30°	1052.9
32.5°	838.3
35°	611.9
37.5°	417.3
40°	258.2
42.5°	155.0
45°	83.4
47.5°	35.7
50°	15.9
52.5°	11.9
55°	11.9
57.5°	8.0
60°	8.0
62.5°	3.9
65°	3.9
67.5°	3.9
70°	3.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)