

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211150

Luminaire Tested: **LE_4B15D010 EC4B10209727 4LBCSM1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209727 4LBSCM1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1210.1 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211150

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBCSM1B

Luminous Intensity Polar Plot






TEST NUMBER: P211150

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBCSM1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84	99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71	91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61	84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53	77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47	72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41	67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37	62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33	58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30	55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211150

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBCSM1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.3	4.0
10°-20°	137.7	11.4
20°-30°	207.0	17.1
30°-40°	245.6	20.3
40°-50°	243.0	20.1
50°-60°	190.9	15.8
60°-70°	107.0	8.8
70°-80°	30.0	2.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.0	32.5
0°-40°	638.6	52.8
0°-60°	1072.6	88.6
0°-90°	1210.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1210.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	511	
5°	510	48
15°	488	138
25°	449	207
35°	394	246
45°	317	243
55°	215	191
65°	107	107
75°	26	30
85°	0	0
90°	0	



TEST NUMBER: P211150

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBCSM1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	511.0
2.5°	509.2
5°	510.2
7.5°	505.8
10°	500.5
12.5°	494.5
15°	488.5
17.5°	480.6
20°	470.1
22.5°	459.8
25°	449.4
27.5°	438.1
30°	423.4
32.5°	408.7
35°	393.8
37.5°	376.5
40°	356.6
42.5°	337.4
45°	316.7
47.5°	293.2
50°	268.9
52.5°	241.2
55°	215.2
57.5°	185.6
60°	157.9
62.5°	132.7
65°	106.7
67.5°	84.1
70°	62.4
72.5°	42.5
75°	26.0
77.5°	13.0
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)