

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211194

Luminaire Tested: **LE_4B15D010 EC4B10208030 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208030 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1849.1 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211194

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBPS1MW

Luminous Intensity Polar Plot






TEST NUMBER: P211194

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	66	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211194

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	3.8
10°-20°	201.2	10.9
20°-30°	303.1	16.4
30°-40°	360.6	19.5
40°-50°	359.9	19.5
50°-60°	292.7	15.8
60°-70°	180.1	9.7
70°-80°	69.8	3.8
80°-90°	11.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.9	31.1
0°-40°	935.5	50.6
0°-60°	1588.1	85.9
0°-90°	1849.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1849.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	745	
5°	743	71
15°	714	201
25°	660	303
35°	577	361
45°	468	360
55°	328	293
65°	181	180
75°	64	70
85°	9	11
90°	0	



TEST NUMBER: P211194

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	745.0
2.5°	746.1
5°	742.9
7.5°	738.5
10°	733.0
12.5°	723.1
15°	714.3
17.5°	701.2
20°	687.0
22.5°	673.8
25°	659.6
27.5°	639.9
30°	620.1
32.5°	601.5
35°	577.3
37.5°	551.1
40°	527.0
42.5°	497.4
45°	467.8
47.5°	436.0
50°	402.1
52.5°	367.0
55°	327.6
57.5°	289.2
60°	252.0
62.5°	215.9
65°	180.7
67.5°	147.9
70°	117.3
72.5°	88.7
75°	63.6
77.5°	41.6
80°	25.2
82.5°	15.3
85°	8.8
87.5°	4.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)