

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212180

Luminaire Tested: **LE_4B30D010 EC4B30509050 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509050 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3145.4 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212180

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212180

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212180

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	3.8
10°-20°	342.3	10.9
20°-30°	515.5	16.4
30°-40°	613.4	19.5
40°-50°	612.2	19.5
50°-60°	497.9	15.8
60°-70°	306.3	9.7
70°-80°	118.7	3.8
80°-90°	19.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.9	31.1
0°-40°	1591.2	50.6
0°-60°	2701.4	85.9
0°-90°	3145.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3145.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1267	
5°	1264	120
15°	1215	342
25°	1122	516
35°	982	613
45°	796	612
55°	557	498
65°	308	306
75°	108	119
85°	15	19
90°	0	



TEST NUMBER: P212180

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1267.3
2.5°	1269.2
5°	1263.6
7.5°	1256.2
10°	1246.8
12.5°	1230.1
15°	1215.1
17.5°	1192.7
20°	1168.6
22.5°	1146.2
25°	1122.0
27.5°	1088.4
30°	1054.9
32.5°	1023.1
35°	982.2
37.5°	937.4
40°	896.4
42.5°	846.1
45°	795.8
47.5°	741.7
50°	683.9
52.5°	624.3
55°	557.3
57.5°	492.1
60°	428.6
62.5°	367.1
65°	307.5
67.5°	251.6
70°	199.4
72.5°	150.9
75°	108.1
77.5°	70.9
80°	42.9
82.5°	26.1
85°	15.0
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)