

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212192

Luminaire Tested: **LE_4B30D010 EC4B30509050 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509050 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2576.5 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212192

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212192

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212192

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	5.7
10°-20°	409.9	15.9
20°-30°	579.3	22.5
30°-40°	561.2	21.8
40°-50°	378.7	14.7
50°-60°	235.0	9.1
60°-70°	157.1	6.1
70°-80°	86.0	3.3
80°-90°	22.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.9	44.1
0°-40°	1697.1	65.9
0°-60°	2310.8	89.7
0°-90°	2576.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2576.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1561	
5°	1548	147
15°	1454	410
25°	1270	579
35°	903	561
45°	485	379
55°	257	235
65°	157	157
75°	80	86
85°	20	23
90°	0	



TEST NUMBER: P212192

CATALOG NUMBER: LE_4B30D010 EC4B30509050 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1561.4
2.5°	1561.4
5°	1547.9
7.5°	1531.2
10°	1511.1
12.5°	1491.1
15°	1454.3
17.5°	1424.2
20°	1374.1
22.5°	1323.9
25°	1270.4
27.5°	1196.9
30°	1116.6
32.5°	1013.0
35°	902.7
37.5°	792.4
40°	682.1
42.5°	571.6
45°	484.8
47.5°	404.5
50°	344.4
52.5°	294.2
55°	257.4
57.5°	227.4
60°	203.9
62.5°	180.5
65°	157.2
67.5°	137.1
70°	117.0
72.5°	100.3
75°	80.3
77.5°	63.6
80°	46.7
82.5°	33.4
85°	20.1
87.5°	6.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)