

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211221

Luminaire Tested: **LE_4B15D010 EC4B10209030 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209030 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1057.0 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211221

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211221

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211221

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	7.8
10°-20°	217.1	20.5
20°-30°	285.7	27.0
30°-40°	222.4	21.0
40°-50°	108.0	10.2
50°-60°	68.2	6.5
60°-70°	44.0	4.2
70°-80°	23.0	2.2
80°-90°	5.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.7	55.4
0°-40°	808.1	76.5
0°-60°	984.3	93.1
0°-90°	1057.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1057.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	902	
5°	885	83
15°	774	217
25°	630	286
35°	356	222
45°	134	108
55°	76	68
65°	44	44
75°	22	23
85°	5	6
90°	0	



TEST NUMBER: P211221

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	901.8
2.5°	896.7
5°	885.0
7.5°	864.8
10°	838.0
12.5°	807.7
15°	774.2
17.5°	738.9
20°	701.9
22.5°	666.7
25°	629.8
27.5°	582.7
30°	518.9
32.5°	443.4
35°	356.0
37.5°	275.4
40°	213.2
42.5°	166.2
45°	134.3
47.5°	109.2
50°	95.7
52.5°	85.6
55°	75.5
57.5°	67.2
60°	58.8
62.5°	50.3
65°	43.6
67.5°	38.6
70°	31.9
72.5°	26.9
75°	21.8
77.5°	16.8
80°	11.7
82.5°	8.4
85°	5.0
87.5°	1.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)