

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170601

Luminaire Tested: **LDA4A13927D010TE LAR15SP 4LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170601
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26141)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A13927D010TE LAR15SP 4LFC1
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1087.9 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.36
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 22.27
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170601

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P170601

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	95
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92	92	92	92
4	106	101	97	94	104	100	97	94	98	95	93	96	94	92	94	92	91	90	90	90	90
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88	88	88	88
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85	85	85	85
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83	83	83	83
8	96	90	86	83	95	89	86	83	88	85	83	88	85	83	87	84	82	81	81	81	81
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	80	80	80
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	78	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	849987
5°	718682
10°	393844
15°	214990
20°	119763
25°	27668
30°	5355
35°	1551
40°	547
45°	192
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170601

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.1	42.0
10°-20°	478.2	44.0
20°-30°	143.4	13.2
30°-40°	8.3	0.8
40°-50°	1.0	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1078.6	99.1
0°-40°	1086.9	99.9
0°-60°	1087.9	100.0
0°-90°	1087.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1087.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6891	
5°	5804	457
15°	1684	478
25°	203	143
35°	10	8
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170601

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6891.1
1°	6823.3
2°	6700.9
3°	6536.9
4°	6253.2
5°	5804.4
6°	5249.1
7°	4644.8
8°	4083.2
9°	3570.0
10°	3144.5
11°	2776.0
12°	2448.5
13°	2165.5
14°	1912.0
15°	1683.6
17.5°	1223.4
20°	912.4
22.5°	601.5
25°	203.3
27.5°	70.6
30°	37.6
32.5°	18.8
35°	10.3
37.5°	5.7
40°	3.4
42.5°	1.7
45°	1.1
47.5°	0.6
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170601

CATALOG NUMBER: LDA4A13927D010TE LAR15SP 4LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)