

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211292

Luminaire Tested: **LE_4B15D010 EC4B10208035 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208035 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1486.2 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211292

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4L1BWH

Luminous Intensity Polar Plot






TEST NUMBER: P211292

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211292

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.2	6.1
10°-20°	262.8	17.7
20°-30°	387.9	26.1
30°-40°	382.8	25.8
40°-50°	234.2	15.8
50°-60°	89.8	6.0
60°-70°	28.1	1.9
70°-80°	8.3	0.6
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	741.9	49.9
0°-40°	1124.7	75.7
0°-60°	1448.8	97.5
0°-90°	1486.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	958	91
15°	932	263
25°	849	388
35°	621	383
45°	300	234
55°	95	90
65°	26	28
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P211292

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	957.8
2.5°	959.9
5°	957.8
7.5°	955.8
10°	949.8
12.5°	941.7
15°	931.6
17.5°	919.5
20°	901.4
22.5°	881.3
25°	849.0
27.5°	808.6
30°	758.2
32.5°	695.8
35°	621.1
37.5°	538.5
40°	453.7
42.5°	375.0
45°	300.4
47.5°	234.0
50°	177.5
52.5°	131.1
55°	94.8
57.5°	66.6
60°	48.4
62.5°	36.3
65°	26.2
67.5°	20.2
70°	14.2
72.5°	10.1
75°	8.1
77.5°	4.1
80°	4.1
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)