

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170641

Luminaire Tested: **LDA4A28927D010TE LAR25NF 4LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26142)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A28927D010TE LAR25NF 4LFC1
Description: PORTFOLIO 4" Flat Cone, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2287.2 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.47
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170641

CATALOG NUMBER: LDA4A28927D010TE LAR25NF 4LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P170641

CATALOG NUMBER: LDA4A28927D010TE LAR25NF 4LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	99	97	97	97	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	104	100	97	106	102	99	96	100	97	95	98	95	94	95	94	92	91	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	92	89	94	91	88	92	89	87	91	89	87	86	86	86	86
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81	81	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	76	76	76
10	89	82	79	76	88	82	78	76	81	78	76	81	78	76	80	77	75	74	74	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1183958
5°	1087272
10°	812186
15°	540987
20°	293055
25°	69913
30°	16365
35°	4653
40°	1594
45°	576
50°	211
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170641

CATALOG NUMBER: LDA4A28927D010TE LAR25NF 4LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	761.0	33.3
10°-20°	1147.5	50.2
20°-30°	350.4	15.3
30°-40°	25.3	1.1
40°-50°	2.9	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2258.9	98.8
0°-40°	2284.2	99.9
0°-60°	2287.2	100.0
0°-90°	2287.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2287.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9599	
5°	8781	761
15°	4236	1148
25°	514	350
35°	31	25
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170641

CATALOG NUMBER: LDA4A28927D010TE LAR25NF 4LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9598.7
1°	9490.5
2°	9334.7
3°	9217.6
4°	9068.5
5°	8781.3
6°	8420.0
7°	7968.2
8°	7502.0
9°	7004.9
10°	6484.6
11°	5988.6
12°	5534.5
13°	5099.3
14°	4679.5
15°	4236.5
17.5°	3182.6
20°	2232.6
22.5°	1393.0
25°	513.7
27.5°	207.7
30°	114.9
32.5°	57.4
35°	30.9
37.5°	17.7
40°	9.9
42.5°	5.5
45°	3.3
47.5°	1.1
50°	1.1
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170641

CATALOG NUMBER: LDA4A28927D010TE LAR25NF 4LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)