

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170548

Luminaire Tested: **LDA4A28940D010TE LAR25NF 4LAL1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26145)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A28940D010TE LAR25NF 4LAL1
Description: PORTFOLIO 4" Lensed Adjustable, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2600.5 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 44.49
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170548

CATALOG NUMBER: LDA4A28940D010TE LAR25NF 4LAL1

Luminous Intensity Polar Plot





TEST NUMBER: P170548

CATALOG NUMBER: LDA4A28940D010TE LAR25NF 4LAL1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	91	91	91
4	105	100	96	93	103	98	95	92	97	94	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78	78	78	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76	76	76	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74	74	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1512304
5°	1219831
10°	916856
15°	609407
20°	326868
25°	82706
30°	19626
35°	6430
40°	2657
45°	1204
50°	537
55°	301
60°	345
65°	409
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170548

CATALOG NUMBER: LDA4A28940D010TE LAR25NF 4LAL1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	866.0	33.3
10°-20°	1290.4	49.6
20°-30°	403.1	15.5
30°-40°	33.0	1.3
40°-50°	5.7	0.2
50°-60°	1.4	0.1
60°-70°	0.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2559.5	98.4
0°-40°	2592.6	99.7
0°-60°	2599.7	100.0
0°-90°	2600.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2600.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12261	
5°	9852	866
15°	4772	1290
25°	608	403
35°	43	33
45°	7	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170548

CATALOG NUMBER: LDA4A28940D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (FULL):

	0°
0°	12260.7
1°	12018.2
2°	11432.5
3°	10817.9
4°	10310.8
5°	9851.9
6°	9423.3
7°	8961.6
8°	8438.0
9°	7895.0
10°	7320.3
11°	6770.5
12°	6253.7
13°	5754.8
14°	5261.5
15°	4772.3
17.5°	3558.2
20°	2490.2
22.5°	1613.7
25°	607.7
27.5°	242.5
30°	137.8
32.5°	73.0
35°	42.7
37.5°	26.2
40°	16.5
42.5°	9.6
45°	6.9
47.5°	4.1
50°	2.8
52.5°	1.4
55°	1.4
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P170548

CATALOG NUMBER: LDA4A28940D010TE LAR25NF 4LAL1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)