

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211280

Luminaire Tested: **LE_4B15D010 EC4B10208035 4LBN1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208035 4LBN1WH
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1167.5 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211280

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211280

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107		112	109	107	105		105	104	102			102	100	99			98
2	109	105	101	98		107	103	100	97		100	97	95			97	95	93			94
3	104	98	94	90		102	97	93	90		94	91	88			92	89	87			90
4	100	93	88	84		98	92	87	83		90	86	82			88	84	82			86
5	95	88	82	78		94	87	82	78		85	81	77			83	80	77			82
6	91	83	78	74		90	82	77	74		81	76	73			79	76	73			78
7	87	79	73	70		86	78	73	69		77	72	69			76	72	69			75
8	84	75	70	66		82	74	69	66		73	69	65			72	68	65			71
9	80	71	66	62		79	71	66	62		70	65	62			69	65	62			68
10	77	68	63	59		76	68	63	59		67	62	59			66	62	59			66

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211280

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.9	17.4
10°-20°	380.6	32.6
20°-30°	341.5	29.3
30°-40°	196.0	16.8
40°-50°	39.1	3.3
50°-60°	4.9	0.4
60°-70°	2.2	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.0	79.2
0°-40°	1121.0	96.0
0°-60°	1165.0	99.8
0°-90°	1167.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1167.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2481	
5°	2282	203
15°	1367	381
25°	738	342
35°	310	196
45°	42	39
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211280

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2481.2
2.5°	2430.9
5°	2281.7
7.5°	2064.0
10°	1826.2
12.5°	1592.3
15°	1366.6
17.5°	1169.0
20°	999.8
22.5°	858.6
25°	737.8
27.5°	641.0
30°	534.2
32.5°	425.3
35°	310.4
37.5°	211.6
40°	131.0
42.5°	78.6
45°	42.3
47.5°	18.1
50°	8.1
52.5°	6.0
55°	6.0
57.5°	4.1
60°	4.1
62.5°	2.0
65°	2.0
67.5°	2.0
70°	2.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)