

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274268

Luminaire Tested: **LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35290)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 803.7 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274268

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274268

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138444
5°	136089
10°	125036
15°	104711
20°	83891
25°	67403
30°	50175
35°	28664
40°	13450
45°	5717
50°	1819
55°	933
60°	634
65°	491
70°	319
75°	0
80°	0
85°	0



TEST NUMBER: P274268

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	14.3
10°-20°	256.5	31.9
20°-30°	255.0	31.7
30°-40°	138.9	17.3
40°-50°	32.1	4.0
50°-60°	4.5	0.6
60°-70°	1.7	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.2	77.9
0°-40°	765.0	95.2
0°-60°	801.7	99.7
0°-90°	803.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1267	
5°	1241	115
15°	926	256
25°	559	255
35°	215	139
45°	37	32
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P274268

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBM0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1267.1
2.5°	1264.1
5°	1240.8
7.5°	1193.2
10°	1127.0
12.5°	1029.8
15°	925.7
17.5°	822.7
20°	721.5
22.5°	638.9
25°	559.1
27.5°	483.3
30°	397.7
32.5°	302.4
35°	214.9
37.5°	144.9
40°	94.3
42.5°	59.3
45°	37.0
47.5°	21.4
50°	10.7
52.5°	5.8
55°	4.9
57.5°	2.9
60°	2.9
62.5°	1.9
65°	1.9
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)