

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274262

Luminaire Tested: **LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1808-906-1)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 533.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274262

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P274262

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	65	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79258
5°	76522
10°	69752
15°	61783
20°	53648
25°	45401
30°	35906
35°	22635
40°	11653
45°	5145
50°	2023
55°	1200
60°	699
65°	414
70°	256
75°	338
80°	0
85°	0



TEST NUMBER: P274262

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.4	12.1
10°-20°	152.3	28.6
20°-30°	171.7	32.2
30°-40°	107.5	20.2
40°-50°	28.7	5.4
50°-60°	6.1	1.1
60°-70°	1.9	0.4
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.3	72.8
0°-40°	495.8	93.0
0°-60°	530.6	99.6
0°-90°	533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	725	
5°	698	64
15°	546	152
25°	377	172
35°	170	108
45°	33	29
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274262

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	725.4
2.5°	719.1
5°	697.7
7.5°	666.0
10°	628.7
12.5°	587.5
15°	546.2
17.5°	504.2
20°	461.4
22.5°	418.6
25°	376.6
27.5°	335.4
30°	284.6
32.5°	227.5
35°	169.7
37.5°	120.5
40°	81.7
42.5°	53.1
45°	33.3
47.5°	19.0
50°	11.9
52.5°	8.7
55°	6.3
57.5°	4.8
60°	3.2
62.5°	2.4
65°	1.6
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)