

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211331

Luminaire Tested: **LE_4B15D010 EC4B10208040 4LBM1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4LBM1MW
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1406.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211331

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBM1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211331

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBM1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	92	88	102	96	91	87	93	89	85		89	86	83		87
3	97	89	83	77	95	87	82	77	85	80	76		82	78	74		80
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	67	62	83	74	67	62	72	66	61		70	65	61		68
6	80	69	62	56	78	68	61	56	66	60	56		65	59	55		63
7	75	64	57	52	74	63	56	51	62	56	51		60	55	51		59
8	71	59	52	47	69	59	52	47	58	51	47		56	51	47		55
9	67	55	48	44	66	55	48	44	54	48	44		53	47	43		52
10	63	52	45	41	62	51	45	41	51	45	40		50	44	40		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211331

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBM1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	7.0
10°-20°	265.2	18.9
20°-30°	352.7	25.1
30°-40°	288.5	20.5
40°-50°	168.0	11.9
50°-60°	111.4	7.9
60°-70°	73.3	5.2
70°-80°	38.7	2.8
80°-90°	9.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.9	51.0
0°-40°	1005.3	71.5
0°-60°	1284.7	91.4
0°-90°	1406.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1406.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1067	
5°	1055	99
15°	945	265
25°	774	353
35°	460	288
45°	212	168
55°	124	111
65°	73	73
75°	37	39
85°	8	9
90°	0	



TEST NUMBER: P211331

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBM1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1067.4
2.5°	1065.5
5°	1055.3
7.5°	1030.8
10°	1004.3
12.5°	979.9
15°	945.2
17.5°	906.5
20°	873.9
22.5°	829.1
25°	774.1
27.5°	715.0
30°	639.6
32.5°	550.1
35°	460.4
37.5°	378.9
40°	307.6
42.5°	252.6
45°	211.8
47.5°	179.2
50°	156.8
52.5°	138.5
55°	124.2
57.5°	110.0
60°	95.7
62.5°	85.6
65°	73.3
67.5°	63.1
70°	53.0
72.5°	44.8
75°	36.7
77.5°	28.5
80°	20.4
82.5°	14.3
85°	8.1
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)