

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211337

Luminaire Tested: **LE_4B15D010 EC4B10208040 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1281.8 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211337

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211337

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211337

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	7.8
10°-20°	263.2	20.5
20°-30°	346.4	27.0
30°-40°	269.7	21.0
40°-50°	131.0	10.2
50°-60°	82.7	6.5
60°-70°	53.4	4.2
70°-80°	27.9	2.2
80°-90°	6.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.2	55.4
0°-40°	979.9	76.4
0°-60°	1193.6	93.1
0°-90°	1281.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1094	
5°	1073	101
15°	939	263
25°	764	346
35°	432	270
45°	163	131
55°	92	83
65°	53	53
75°	26	28
85°	6	7
90°	0	



TEST NUMBER: P211337

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1093.5
2.5°	1087.4
5°	1073.1
7.5°	1048.8
10°	1016.2
12.5°	979.5
15°	938.8
17.5°	896.0
20°	851.2
22.5°	808.4
25°	763.6
27.5°	706.6
30°	629.2
32.5°	537.5
35°	431.8
37.5°	334.0
40°	258.6
42.5°	201.6
45°	162.9
47.5°	132.4
50°	116.1
52.5°	103.8
55°	91.6
57.5°	81.4
60°	71.2
62.5°	61.1
65°	52.9
67.5°	46.9
70°	38.7
72.5°	32.6
75°	26.4
77.5°	20.4
80°	14.3
82.5°	10.2
85°	6.1
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)