

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274286

Luminaire Tested: **LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35167)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.7 lumens
Efficiency: N/A
Efficacy: 50.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274286

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P274286

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 | | | |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 95 | 91 | 88 | 91 | 88 | 86 | 89 | 86 | 84 | 82 | | | |
| 3 | 99 | 91 | 85 | 80 | 97 | 90 | 84 | 80 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 | | | |
| 4 | 92 | 83 | 77 | 72 | 90 | 82 | 76 | 71 | 80 | 75 | 70 | 78 | 73 | 70 | 76 | 72 | 69 | 67 | | | |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 64 | 74 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 62 | 61 | | | |
| 6 | 81 | 71 | 64 | 58 | 80 | 70 | 63 | 58 | 68 | 62 | 58 | 67 | 61 | 57 | 65 | 61 | 57 | 55 | | | |
| 7 | 76 | 65 | 58 | 53 | 75 | 65 | 58 | 53 | 63 | 57 | 53 | 62 | 56 | 52 | 61 | 56 | 52 | 50 | | | |
| 8 | 72 | 60 | 53 | 49 | 70 | 60 | 53 | 49 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 46 | | | |
| 9 | 68 | 56 | 49 | 45 | 66 | 56 | 49 | 45 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 43 | | | |
| 10 | 64 | 52 | 46 | 41 | 63 | 52 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 49 | 44 | 41 | 39 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 50052 |
| 5° | 50244 |
| 10° | 50392 |
| 15° | 50393 |
| 20° | 50125 |
| 25° | 48946 |
| 30° | 45747 |
| 35° | 39615 |
| 40° | 30951 |
| 45° | 22204 |
| 50° | 14431 |
| 55° | 8629 |
| 60° | 5048 |
| 65° | 3232 |
| 70° | 2172 |
| 75° | 1646 |
| 80° | 1195 |
| 85° | 0 |



TEST NUMBER: P274286

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 43.6 | 6.1 |
| 10°-20° | 125.7 | 17.7 |
| 20°-30° | 185.5 | 26.1 |
| 30°-40° | 183.0 | 25.8 |
| 40°-50° | 112.0 | 15.8 |
| 50°-60° | 42.9 | 6.0 |
| 60°-70° | 13.4 | 1.9 |
| 70°-80° | 3.9 | 0.6 |
| 80°-90° | 0.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 354.8 | 49.9 |
| 0°-40° | 537.8 | 75.7 |
| 0°-60° | 692.8 | 97.5 |
| 0°-90° | 710.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 710.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 458 | |
| 5° | 458 | 44 |
| 15° | 446 | 126 |
| 25° | 406 | 185 |
| 35° | 297 | 183 |
| 45° | 144 | 112 |
| 55° | 45 | 43 |
| 65° | 12 | 13 |
| 75° | 4 | 4 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P274286

CATALOG NUMBER: LD4B10DE010W2N2050 EU4B1020W2N902050 4LBW0H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 458.1 |
| 2.5° | 459.0 |
| 5° | 458.1 |
| 7.5° | 457.1 |
| 10° | 454.2 |
| 12.5° | 450.3 |
| 15° | 445.5 |
| 17.5° | 439.7 |
| 20° | 431.1 |
| 22.5° | 421.4 |
| 25° | 406.0 |
| 27.5° | 386.7 |
| 30° | 362.6 |
| 32.5° | 332.7 |
| 35° | 297.0 |
| 37.5° | 257.5 |
| 40° | 217.0 |
| 42.5° | 179.4 |
| 45° | 143.7 |
| 47.5° | 111.9 |
| 50° | 84.9 |
| 52.5° | 62.7 |
| 55° | 45.3 |
| 57.5° | 31.8 |
| 60° | 23.1 |
| 62.5° | 17.4 |
| 65° | 12.5 |
| 67.5° | 9.6 |
| 70° | 6.8 |
| 72.5° | 4.8 |
| 75° | 3.9 |
| 77.5° | 1.9 |
| 80° | 1.9 |
| 82.5° | 1.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)