

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211363

Luminaire Tested: **LE_4B15D010 EC4B10209040 4LBN1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209040 4LBN1GPH
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.1 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211363

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211363

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211363

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	10.9
10°-20°	192.7	27.3
20°-30°	234.9	33.3
30°-40°	155.0	22.0
40°-50°	35.7	5.1
50°-60°	6.8	1.0
60°-70°	2.5	0.4
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.5	71.6
0°-40°	659.5	93.5
0°-60°	701.9	99.5
0°-90°	705.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	825	77
15°	690	193
25°	516	235
35°	248	155
45°	39	36
55°	7	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P211363

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	845.6
2.5°	843.9
5°	825.1
7.5°	799.5
10°	765.4
12.5°	731.1
15°	690.2
17.5°	647.4
20°	603.1
22.5°	563.8
25°	515.9
27.5°	468.1
30°	406.6
32.5°	331.4
35°	247.7
37.5°	172.5
40°	111.0
42.5°	68.3
45°	39.3
47.5°	20.5
50°	11.9
52.5°	10.2
55°	6.8
57.5°	5.1
60°	5.1
62.5°	3.4
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)