

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274313

Luminaire Tested: **LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35143)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, CAST SHALLOW WITH MATTE BLACK FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 917.3 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274313

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

Luminous Intensity Polar Plot





TEST NUMBER: P274313

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37755
5°	37831
10°	37556
15°	37362
20°	36963
25°	36637
30°	36112
35°	35526
40°	34388
45°	33078
50°	30915
55°	27713
60°	23331
65°	18656
70°	13507
75°	7418
80°	1459
85°	0



TEST NUMBER: P274313

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	4.0
10°-20°	104.4	11.4
20°-30°	156.9	17.1
30°-40°	186.2	20.3
40°-50°	184.2	20.1
50°-60°	144.7	15.8
60°-70°	81.1	8.8
70°-80°	22.8	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	297.9	32.5
0°-40°	484.1	52.8
0°-60°	813.0	88.6
0°-90°	917.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	917.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	387	
5°	387	37
15°	370	104
25°	341	157
35°	299	186
45°	240	184
55°	163	145
65°	81	81
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P274313

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBCS0MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	387.4
2.5°	386.0
5°	386.7
7.5°	383.4
10°	379.5
12.5°	374.9
15°	370.3
17.5°	364.3
20°	356.4
22.5°	348.6
25°	340.7
27.5°	332.1
30°	320.9
32.5°	309.7
35°	298.6
37.5°	285.4
40°	270.3
42.5°	255.8
45°	240.0
47.5°	222.3
50°	203.9
52.5°	182.8
55°	163.1
57.5°	140.7
60°	119.7
62.5°	100.6
65°	80.9
67.5°	63.8
70°	47.4
72.5°	32.2
75°	19.7
77.5°	9.9
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)