

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274277

Luminaire Tested: **LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35289)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1066.6 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274277

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274277

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71413
5°	72618
10°	75898
15°	80561
20°	84089
25°	83352
30°	77527
35°	66318
40°	50534
45°	29637
50°	12663
55°	3715
60°	1071
65°	620
70°	383
75°	507
80°	0
85°	0



TEST NUMBER: P274277

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	6.0
10°-20°	201.7	18.9
20°-30°	314.6	29.5
30°-40°	306.2	28.7
40°-50°	152.9	14.3
50°-60°	23.7	2.2
60°-70°	2.8	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	580.3	54.4
0°-40°	886.4	83.1
0°-60°	1063.0	99.7
0°-90°	1066.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	662	64
15°	712	202
25°	691	315
35°	497	306
45°	192	153
55°	20	24
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274277

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	653.6
2.5°	656.0
5°	662.1
7.5°	671.9
10°	684.1
12.5°	700.0
15°	712.2
17.5°	722.0
20°	723.2
22.5°	714.6
25°	691.4
27.5°	657.2
30°	614.5
32.5°	560.7
35°	497.2
37.5°	427.6
40°	354.3
42.5°	276.1
45°	191.8
47.5°	123.4
50°	74.5
52.5°	40.3
55°	19.5
57.5°	8.6
60°	4.9
62.5°	3.7
65°	2.4
67.5°	2.4
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)