

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274281

Luminaire Tested: **LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274281
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35289)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1219.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274281

CATALOG NUMBER: LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274281

CATALOG NUMBER: LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81607
5°	82993
10°	86738
15°	92076
20°	96100
25°	95263
30°	88605
35°	75788
40°	57751
45°	33870
50°	14482
55°	4248
60°	1224
65°	724
70°	447
75°	591
80°	0
85°	0



TEST NUMBER: P274281

CATALOG NUMBER: LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	6.0
10°-20°	230.5	18.9
20°-30°	359.6	29.5
30°-40°	349.9	28.7
40°-50°	174.8	14.3
50°-60°	27.1	2.2
60°-70°	3.3	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.2	54.4
0°-40°	1013.0	83.1
0°-60°	1214.9	99.7
0°-90°	1219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	747	
5°	757	73
15°	814	231
25°	790	360
35°	568	350
45°	219	175
55°	22	27
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274281

CATALOG NUMBER: LD4B15DE010W2N2050 EU4B1020W2N902050 4LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	746.9
2.5°	749.7
5°	756.7
7.5°	767.9
10°	781.8
12.5°	800.0
15°	814.0
17.5°	825.1
20°	826.5
22.5°	816.7
25°	790.2
27.5°	751.1
30°	702.3
32.5°	640.8
35°	568.2
37.5°	488.6
40°	404.9
42.5°	315.5
45°	219.2
47.5°	141.0
50°	85.2
52.5°	46.1
55°	22.3
57.5°	9.8
60°	5.6
62.5°	4.2
65°	2.8
67.5°	2.8
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)