

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211408

Luminaire Tested: **LE_4B15D010 EC4B10208050 4LBW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208050 4LBW1LI
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1778.2 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211408

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211408

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211408

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.5	6.0
10°-20°	336.2	18.9
20°-30°	524.5	29.5
30°-40°	510.3	28.7
40°-50°	254.9	14.3
50°-60°	39.5	2.2
60°-70°	4.8	0.3
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.3	54.4
0°-40°	1477.6	83.1
0°-60°	1772.0	99.7
0°-90°	1778.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1778.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1090	
5°	1104	107
15°	1187	336
25°	1153	525
35°	829	510
45°	320	255
55°	33	39
65°	4	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P211408

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1089.5
2.5°	1093.5
5°	1103.7
7.5°	1120.1
10°	1140.4
12.5°	1166.8
15°	1187.3
17.5°	1203.5
20°	1205.6
22.5°	1191.3
25°	1152.6
27.5°	1095.6
30°	1024.3
32.5°	934.7
35°	828.8
37.5°	712.7
40°	590.6
42.5°	460.3
45°	319.7
47.5°	205.7
50°	124.2
52.5°	67.2
55°	32.6
57.5°	14.3
60°	8.1
62.5°	6.1
65°	4.1
67.5°	4.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)