

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211552

Luminaire Tested: **LE_4B20D010 EC4B10209727 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209727 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1402.5 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211552

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P211552

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 | | | |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 95 | 91 | 88 | 91 | 88 | 86 | 89 | 86 | 84 | 82 | | | |
| 3 | 99 | 91 | 85 | 80 | 97 | 90 | 84 | 80 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 74 | | | |
| 4 | 92 | 83 | 77 | 72 | 90 | 82 | 76 | 71 | 80 | 75 | 70 | 78 | 73 | 70 | 76 | 72 | 69 | 67 | | | |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 64 | 74 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 62 | 61 | | | |
| 6 | 81 | 71 | 64 | 58 | 80 | 70 | 63 | 58 | 68 | 62 | 58 | 67 | 61 | 57 | 65 | 61 | 57 | 55 | | | |
| 7 | 76 | 65 | 58 | 53 | 75 | 65 | 58 | 53 | 63 | 57 | 53 | 62 | 56 | 52 | 61 | 56 | 52 | 50 | | | |
| 8 | 72 | 60 | 53 | 49 | 70 | 60 | 53 | 49 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 46 | | | |
| 9 | 68 | 56 | 49 | 45 | 66 | 56 | 49 | 45 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 43 | | | |
| 10 | 64 | 52 | 46 | 41 | 63 | 52 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 49 | 44 | 41 | 39 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211552

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4L1BWH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 86.1 | 6.1 |
| 10°-20° | 248.1 | 17.7 |
| 20°-30° | 366.1 | 26.1 |
| 30°-40° | 361.2 | 25.8 |
| 40°-50° | 221.1 | 15.8 |
| 50°-60° | 84.7 | 6.0 |
| 60°-70° | 26.5 | 1.9 |
| 70°-80° | 7.8 | 0.6 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 700.2 | 49.9 |
| 0°-40° | 1061.5 | 75.7 |
| 0°-60° | 1367.3 | 97.5 |
| 0°-90° | 1402.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1402.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 904 | |
| 5° | 904 | 86 |
| 15° | 879 | 248 |
| 25° | 801 | 366 |
| 35° | 586 | 361 |
| 45° | 284 | 221 |
| 55° | 89 | 85 |
| 65° | 25 | 26 |
| 75° | 8 | 8 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P211552

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4L1BWH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 904.0 |
| 2.5° | 906.0 |
| 5° | 904.0 |
| 7.5° | 902.1 |
| 10° | 896.4 |
| 12.5° | 888.8 |
| 15° | 879.3 |
| 17.5° | 867.9 |
| 20° | 850.7 |
| 22.5° | 831.7 |
| 25° | 801.2 |
| 27.5° | 763.2 |
| 30° | 715.6 |
| 32.5° | 656.6 |
| 35° | 586.1 |
| 37.5° | 508.2 |
| 40° | 428.3 |
| 42.5° | 354.0 |
| 45° | 283.6 |
| 47.5° | 220.7 |
| 50° | 167.5 |
| 52.5° | 123.7 |
| 55° | 89.4 |
| 57.5° | 62.8 |
| 60° | 45.7 |
| 62.5° | 34.2 |
| 65° | 24.7 |
| 67.5° | 19.0 |
| 70° | 13.3 |
| 72.5° | 9.5 |
| 75° | 7.7 |
| 77.5° | 3.8 |
| 80° | 3.8 |
| 82.5° | 1.9 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)