

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211547

Luminaire Tested: **LE\_4B20D010 EC4B10209727 4LBS1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211547  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209727 4LBS1MW  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1718.5 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211547

CATALOG NUMBER: LE\_4B20D010 EC4B10209727 4LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P211547

CATALOG NUMBER: LE\_4B20D010 EC4B10209727 4LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211547

CATALOG NUMBER: LE\_4B20D010 EC4B10209727 4LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.6	3.8
10°-20°	187.0	10.9
20°-30°	281.6	16.4
30°-40°	335.1	19.5
40°-50°	334.5	19.5
50°-60°	272.1	15.8
60°-70°	167.4	9.7
70°-80°	64.8	3.8
80°-90°	10.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.2	31.1
0°-40°	869.4	50.6
0°-60°	1475.9	85.9
0°-90°	1718.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1718.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	692	
5°	690	66
15°	664	187
25°	613	282
35°	537	335
45°	435	335
55°	304	272
65°	168	167
75°	59	65
85°	8	10
90°	0	



TEST NUMBER: P211547

CATALOG NUMBER: LE\_4B20D010 EC4B10209727 4LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	692.4
2.5°	693.4
5°	690.3
7.5°	686.3
10°	681.2
12.5°	672.0
15°	663.9
17.5°	651.7
20°	638.5
22.5°	626.2
25°	612.9
27.5°	594.6
30°	576.3
32.5°	559.0
35°	536.6
37.5°	512.1
40°	489.8
42.5°	462.3
45°	434.8
47.5°	405.3
50°	373.6
52.5°	341.2
55°	304.5
57.5°	268.8
60°	234.2
62.5°	200.6
65°	168.0
67.5°	137.5
70°	108.9
72.5°	82.5
75°	59.0
77.5°	38.7
80°	23.4
82.5°	14.3
85°	8.1
87.5°	4.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)