

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211567

Luminaire Tested: **LE_4B20D010 EC4B10208030 4LBN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208030 4LBN1H
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1468.2 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211567

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBN1H

Luminous Intensity Polar Plot





TEST NUMBER: P211567

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211567

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	11.3
10°-20°	403.4	27.5
20°-30°	468.4	31.9
30°-40°	310.2	21.1
40°-50°	87.0	5.9
50°-60°	21.9	1.5
60°-70°	8.2	0.6
70°-80°	2.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.1	70.7
0°-40°	1348.3	91.8
0°-60°	1457.1	99.2
0°-90°	1468.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1843	
5°	1795	166
15°	1444	403
25°	1027	468
35°	497	310
45°	101	87
55°	24	22
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P211567

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1843.4
2.5°	1835.4
5°	1795.4
7.5°	1726.3
10°	1641.2
12.5°	1545.5
15°	1444.3
17.5°	1345.9
20°	1236.9
22.5°	1135.8
25°	1026.7
27.5°	923.0
30°	790.0
32.5°	649.0
35°	497.4
37.5°	356.5
40°	242.1
42.5°	156.9
45°	101.0
47.5°	61.1
50°	39.9
52.5°	29.2
55°	23.9
57.5°	18.7
60°	13.3
62.5°	10.7
65°	8.0
67.5°	5.3
70°	5.3
72.5°	2.7
75°	2.7
77.5°	2.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)